



# Subway 3.0 TwistFlush Wall Faced Toilet

S & P Trap | TwistFlush | CeramicPlus | Soft Close Seat

## Product Image



## Product Details

<b>Code:</b>	<b>4671T1R1S4B</b>
Brand:	Villeroy & Boch
Range:	Subway 3.0
Warranty:	10 Years*
Product Width:	370 mm
Product Depth:	595 mm
WELS:	4 Star 3.5 LPM, Reg #: L07242

## Additional Features

### Required Product

Matching In Wall Cistern

### Recommended Products

ViConnect 92233300 or 92233400  
Cistern with E100 E200 or E300  
Flushplate


### Additional Notes

- TwistFlush
- Fully Smooth Sided
- CeramicPlus
- Soft Close Seat

### Installation Instructions

- \* S trap set out 100-110mm
- \* P Trap set Out 180mm
- \* S Trap Set out 160-175mm with VT103 Vario order seperately

## Technical Specification



\*Please visit [argentaust.com.au/warranty](http://argentaust.com.au/warranty) to view the full warranty

*Note: All dimensions are in millimetres and are subject to normal manufacturing variations. Always use the physical product measurements for cut-outs and rough-ins as the technical details shown may differ from the actual product. Use acetic cured silicone sealant. Do not use epoxy type adhesives. Clean with damp cloth. Do not use abrasive cleaners, liquids or pastes.*





# Argent 80 In Wall Cistern - Mechanical

## Product Image



## Product Details

<b>Code:</b>	<b>IN38905</b>
<b>Brand:</b>	Argent
<b>Range:</b>	In Wall
<b>Warranty:</b>	15 Years*
<b>WELS:</b>	4 Star 3.5 LPM, Reg #: L05256

## Additional Features

### Required Product

Suitable matching pan


### Recommended Products

Argent Wall faced Pan

### Additional Notes

- Suits Kubic and Round and Edge Flush Plates
- Kubic and Round Flush Plates available in many popular colours

## Technical Specification



\*Please visit [argentaust.com.au/warranty](http://argentaust.com.au/warranty) to view the full warranty

Note: All dimensions are in millimetres and are subject to normal manufacturing variations. It is recommended to use the physical product measurements for cut-outs and rough-ins as the technical details shown may differ from the actual product. Use acetic cured silicone sealant. Do not use epoxy type adhesives. Clean with damp cloth. Do not use abrasive cleaners, liquids or pastes.